



# ECLIPSE

## 2-WAY STEPPER-CONTROLLED PROPORTIONAL ISOLATION VALVES



Utilizing the industry's most robust and powerful miniature linear actuator, the patent pending stepper-controlled proportional valve leads the industry in performance, durability and precise flow control.

This valve is ideal in critical applications for liquid and gas delivery, medical, analytical and industrial automation requiring high resolution and excellent repeatability. In addition, the unique design allows for custom flow profiles.

<b>Medium</b>	Liquids and gases
<b>Typical Cycle Time for Full Travel</b>	1.1 seconds at 1,000 steps per second
<b>Material, Wetted</b>	Ceramic (others depending on porting option)
<b>Operating Pressure</b>	Vacuum to 30 psig*
<b>Proof Pressure (Overpressure)</b>	50 psig
<b>Flow*</b>	Air: 0 to 7 l/min -0/+10% (0.247 scfm) @ 30 psig Water: 0 to 190 ml/min -0/+10% (0.0067 scfm) @ 30 psig
<b>Flow Resolution</b>	0.19 ml/min water and 0.007 l/min air max @ 30 psig per full step depending on pressure
<b>Position Resolution</b>	0.00006" per step
<b>Ambient/Environment</b>	32 to 180°F
<b>Driver</b>	Bipolar chopper drive required
<b>Supply Voltage to Motor Driver</b>	20 VDC @ 30 psig
<b>Current/Phase</b>	0.49 amps
<b>Mount</b>	Manifold or flat bottom (ZDVF)
<b>Wattage</b>	2.5 watts nominal only during adjustment. Zero power consumption to maintain position.
<b>Material, Seals</b>	Valve: None Port: FKM standard. EPDM and others upon request
<b>More Details</b>	<a href="http://clippard.com/link/eiv">clippard.com/link/eiv</a>

\*This product is highly modifiable for OEM applications including alternate body materials, flow profiles, pressure ranges, manifold mounting, etc. Please consult Clippard.

- Leak free (<0.05 sccm)
- Excellent Linearity (<4% of full-scale)
- Fast Response (<2 ms reaction time)
- Cycle Life of Typically >1 million
- Repeatability: <0.5% of Full Travel



Design World 2020 Leadership  
in Engineering Achievement  
Program Winner



**Clippard**

877-245-6247 | [clippard.com](http://clippard.com)



## ORDERING INFORMATION

Series	Porting	Seals
<b>EIVU</b> Eclipse Valve	<b>-M</b> Manifold <b>-Z</b> Zero Dead Volume Fitting (ZDVF)	<b>-ENS</b> ZDVF Porting <b>-V-ENS</b> FKM
<b>Example Part No.</b> EIVU-M-V-ENS		

### EIVU-M Series



### EIVU-Z Series




#### Clippard Accessories


- EUM-01** Single-Station Manifold, #10-32
- M-EUM-01** Single-Station Manifold, M5x0.8
- SCPVD-1** Bipolar Chopper Driver
- ZDVF-18** Headless 1/4-28 Flatbottom Fitting, 1/8" OD (IDEX p/n XP-348)

#### Other Recommended Accessory

- Miniature optical encoder from US Digital for 4 mm bore with metric screws (p/n E4T)



#### Manifold Layout



877-245-6247 | [clippard.com](http://clippard.com)

CLIPPARD INSTRUMENT LABORATORY, INC. • ISO 9001 • TDS 10.19  
For warranty and disclaimer information, visit [clippard.com/warranty](http://clippard.com/warranty)

